

MAXTECH

DNP400x90-Ø10 NL129 yellow with axle

EAN 4031582438208



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread Material Mix	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	400 mm
Tread width	90 mm
Axle Hole Diameter	10 mm
Hub Length	129 mm

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Load capacity at 3 km/h	145 kg
Electric Conductive	No
Stainless	No
Load capacity Static	190 kg
Overall weight	3.62 kg

MAXTECH

DNP400x90-Ø10 NL129 yellow with axle

EAN 4031582438208



BETTER MOBILITY. BETTER LIFE.

Product Drawings

