

ALPHA

3477IER160P63 TFR

EAN 4031582390933



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Load capacity Static	700 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	200 mm
Overall weight	2.93 kg

WHEEL

Body material	Aluminium
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Hardness of tread (A)	70 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	55 mm
Swivel radius	167 mm
Swivel interference	334 mm

FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ALPHA

3477IER160P63 TFR

EAN 4031582390933



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

