

PRODUCT INFORMATION

PURETECH

PIR 125x37-Ø12 HL48

EAN 4031582320350



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	1.04 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.46 in
Axle hole diameter	0.47 in
Hub length	1.89 in
Body width	1.46 in
Hardness of tread (A)	80 Shore A

PURETECH

PIR 125x37-Ø12 HL48

EAN 4031582320350

Order number 00030824
Product Drawings



BETTER MOBILITY. BETTER LIFE.

