

# SUPRATECH

PJP125X40-Ø8,3 HL45

EAN 4031582444186



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

## WHEEL

Body material	Polypropylene
	soft
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.31 in
Hub length	1.77 in
Hardness of tread (A)	65 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Supratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	396.83 lb
Load capacity Static	793.66 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.53 lb

# SUPRATECH

PJP125X40-Ø8,3 HL45

EAN 4031582444186



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

