

STEM

S70-10x10 / 8

EAN 4031582321869



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

| | |
|---------------|--------------------------------------|
| Fitting type | Threaded stem with hexagon neck, top |
| Stem diameter | 10 mm |
| Stem length | 10 mm |

PERFORMANCE

Corrosion Resistance ● ● ● ○ ○

CORE ATTRIBUTES

| | |
|-------------------------|-----------|
| Product Name | Stem |
| Type | Accessory |
| Load capacity at 3 km/h | 40 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 80 kg |
| Overall Height | 6 mm |
| Overall weight | 0.02 kg |