

STEM

S70-10x10 / 8

EAN 4031582321869



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion Resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Stem
Type	Accessory
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Overall Height	6 mm
Overall weight	0.02 kg

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	10 mm