

MAXTECH

PAO100X25-Ø6X27 + ASBUS

EAN 4031582381245



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.11 kg

WHEEL

Diameter	100 mm
Tread width	25 mm
Axle hole diameter	6 mm
Hub length	27 mm