

# ELASTECH

UER125x40-Ø15

EAN 4031582337952



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

### CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Elastech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 551.16 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 1102.31 lb                    |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 176 °F                        |
| Overall weight              | 0.95 lb                       |

### WHEEL

|                    |                                 |
|--------------------|---------------------------------|
| Body material      | Polyamide                       |
| Tread material     | Elastic tire, black, vulcanized |
| Bearing            | Roller bearing                  |
| Threadguards       | Without threadguard             |
| Diameter           | 4.92 in                         |
| Tread width        | 1.57 in                         |
| Axle hole diameter | 0.59 in                         |
| Hub length         | 2.28 in                         |

