PRODUCT INFORMATION

STYLEA

5925UAP100L51-11 DOM41

EAN 4031582370652



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Stylea
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	101 mm
Overall width	75 mm

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Swivel radius	112 mm
Swivel interference	224 mm
Dome diameter	41 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Precision ball bearing
Axle	Riveted
Threadguards	With threadguard
Diameter	100 mm
Tread width	20 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	11 mm

© Copyright 2026 TENTE International GmbH


STYLEA

5925UAP100L51-11 DOM41

EAN 4031582370652

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH