

DURATECH

TOO 100X50-Ø20 HL60

EAN 4031582322491
Order number 00804809



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	100 mm
Tread width	50 mm
Axle hole diameter	20 mm
Hub length	60 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	720 kg
Load capacity at 6 km/h	600 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.38 kg

DURATECH

TOO 100X50-Ø20 HL60

EAN 4031582322491
Order number 00804809



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

