

NOVATECH

FTX140X60-Ø12 HL65-A

EAN 4031582332070



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Casting
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj, zapečaceno
stitnici omotaca	Sa threadguard
Prečnik	140 mm
Širina omotac	60 mm
dimenzija rupa osovina	12 mm
dužina glavcine	65 mm
Teškoća gazećeg omotac (A)	92 Šor A
Tip ležaja	6006 2RS
Tip zaptivke	A
Pogodno za	bt_linde

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip kućišta	Tocak
Nosivost na 3 km/h	700 kg
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	2,99 kg

NOVATECH

FTX140X60-Ø12 HL65-A

EAN 4031582332070



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

