PRODUCT INFORMATION

LINEA

594CUAC125P51 RAL9002

EAN 4031582398625

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Linea
Type	Swivel caster with combined lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	286.6 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	573.2 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	5.83 in
Overall width	3.23 in
Certification	Tested and monitored by TÜV Süd

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Housing Color	Gray white (RAL9002)
Offset	1.57 in
Swivel radius	5.08 in
Swivel interference	10.16 in
Dome diameter	2.05 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	4.92 in
Tread width	0.79 in
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	3.74 in
Plate width	2.76 in
Plate hole length (Maximum)	2.95 in
Plate hole width (Maximum)	1.97 in
Plate hole diameter	0.43 in
Hint	Washable beds must be sealed in the fitting area by the hospital bed manufacturer.

Deutscher Designer Club

Interzum Award

IF Design Award

© Copyright 2026 TENTE International GmbH


LINEA

594CUAC125P51 RAL9002

EAN 4031582398625

BETTER MOBILITY. BETTER LIFE.

Product Drawings



Deutscher Designer Club

Interzum Award

IF Design Award

© Copyright 2026 TENTE International GmbH