PRODUCT INFORMATION

LUMINA

A525POI040P41-38x38/8

EAN 4031582409949



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel caster with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	22.05 lb
Electric conductive	no
Stainless	no
Load capacity Static	44.09 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.13 in
Overall width	1.5 in
Overall weight	0.12 lb

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Swivel radius	1.42 in
Swivel interference	2.83 in

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.57 in
Tread width	0.24 in
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Square plate
Plate length	1.5 in
Plate width	1.5 in
Plate hole length (Maximum)	1.06 in
Plate hole width (Maximum)	1.06 in
Plate hole diameter	0.2 in

© Copyright 2026 TENTE International GmbH