

# DURATECH

TOP 080X60-Ø25 HL60

EAN 4031582331011  
Order number 00827802



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide, heavy          |
| Tread material        | Identical with wheel body |
| Bearing               | Precision ball bearing    |
| Wheel color           | Natural white             |
| Threadguards          | Without threadguard       |
| Diameter              | 3.15 in                   |
| Tread width           | 2.36 in                   |
| Axle hole diameter    | 0.98 in                   |
| Hub length            | 2.36 in                   |
| Body width            | 2.36 in                   |
| Hardness of tread (D) | 75 Shore D                |
| Bearing type          | 6005                      |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ○ ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product name                | Duratech                     |
| Type                        | Wheel                        |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph    | 1322.77 lb                   |
| Load capacity at 3.7 mph    | 1058.22 lb                   |
| Load capacity Static        | 2645.54 lb                   |
| Temperature range (Minimum) | -40 °F                       |
| Temperature range (Maximum) | 176 °F                       |
| Overall weight              | 0.97 lb                      |

# DURATECH

TOP 080X60-Ø25 HL60

EAN 4031582331011  
Order number 00827802



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

