

# NOVATECH

FTF250X80-Ø80-5XØ15

EAN 4031582332124



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	9.043 kg

## WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Flanged wheel
Diameter	250 mm
Tread width	80 mm
Axle hole diameter	80 mm
Hardness of tread (A)	92 Shore A
Hole circle diameter	112 mm
Fitting hole diameter	15 mm
Suitable for	komatsu

## FITTING

Bolt mounting holes quantity	5
------------------------------	---

## TECHNICAL DRAWINGS

