

PRODUCT INFORMATION

ELASTECH

IFP125x50-Ø25

EAN 4031582319804



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES


Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Load capacity at 3.7 mph	529.11 lb
Electric conductive	no
Stainless	no
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	1.86 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Tread hardness	soft
Body material	Aluminum
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.97 in
Axle hole diameter	0.98 in
Hub length	2.36 in
Hardness of tread (A)	68 Shore A




PRODUCT INFORMATION

ELASTECH

IFP125x50-Ø25

EAN 4031582319804

Order number 00340807



BETTER MOBILITY. BETTER LIFE.