

ELASTECH

UEP 200X46-Ø20

EAN 4031582328608
Order number 00023479



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.81 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.81 in
Hardness of tread (A)	63 Shore A

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	881.85 lb
Load capacity Static	1763.7 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	2.74 lb

ELASTECH

UEP 200X46-Ø20

EAN 4031582328608
Order number 00023479



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

