

LEVINA

5377PJP125P50 XL 7001/3000

EAN 4031582404135



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Levina
Type	Swivel caster with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	6.34 in
Overall width	2.32 in
Overall weight	1.4 lb

HOUSING

Housing Material	Polyamide
Fork shape	Slim
Swivel bearing	Two ball races
Housing Color	Silver gray (RAL7001)
Offset	1.5 in
Swivel radius	5.12 in
Swivel interference	10.24 in
Dome diameter	2.32 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.26 in
Body width	1.26 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	3.03 in
Plate width	2.64 in
Plate hole length (Minimum)	1.83 in
Plate hole length (Maximum)	2.03 in
Plate hole width (Minimum)	2.2 in
Plate hole width (Maximum)	2.42 in
Plate hole diameter	0.33 in



Universal
Design
Award



Deutscher
Designer
Club

LEVINA

5377PJP125P50 XL 7001/3000





EAN 4031582404135

Order number 00039498

Product Drawings



BETTER MOBILITY. BETTER LIFE.



Universal
Design
Award



Deutscher
Designer
Club