

FOOTMASTER

FOOT MASTER GD-100-F-NYN

EAN 4031582413243



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	800 kg
Electric Conductive	No
Stainless	No
Load capacity Static	800 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	120 mm
Overall width	98 mm
Overall weight	1.75 kg

HOUSING

Housing Color	White
Offset	53 mm
Swivel radius	90.5 mm
Swivel interference	181 mm
Dome diameter	98 mm

WHEEL

Bearing	Roller bearing, damped
Wheel Color	Black
Diameter	75 mm
Tread width	30 mm
Body width	30 mm

FITTING

Plate length	95 mm
Plate width	95 mm
Plate hole length (Maximum)	70 mm
Plate hole width (Maximum)	70 mm
Plate hole diameter	11 mm

FOOTMASTER

FOOT MASTER GD-100-F-NYN

EAN 4031582413243

Order number 00062070
Product Drawings



BETTER MOBILITY. BETTER LIFE.

