PRODUCT INFORMATION

# GALEA

5070PJP100P30-12

EAN 4031582378627

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●○ |
| Movement noise | ●●●●○ |
| Attrition | ●●●●○ |
| Corrosion resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product name | Galea |
| Type | Swivel caster |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 5.47 in |
| Overall width | 2.6 in |
| Overall weight | 0.96 lb |

## HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Closed |
| Swivel bearing | Two ball races |
| Offset | 1.57 in |
| Swivel radius | 3.54 in |
| Swivel interference | 7.09 in |
| Dome diameter | 2.32 in |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 1.18 in |
| Hardness of tread (A) | 87 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.47 in |

© Copyright 2026 TENTE International GmbH


# GALEA


5070PJP100P30-12

EAN 4031582378627

Order number 00770938

**Product Drawings**



© Copyright 2026 TENTE International GmbH