

ALPHA STAINLESS

8478PID125P62

EAN 4031582381702
Order number 00035730



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha stainless |
| Type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 100 kg |
| Stainless | ✓ |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 155 mm |
| Overall width | 85 mm |
| Overall weight | 0.825 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Solid rubber, non-marking |
| Bearing | Roller bearing, stainless |
| Axle | Screwed with nut |
| Wheel color | Graphite black (RAL9011) |
| Diameter | 125 mm |
| Tread width | 37 mm |
| Body width | 37 mm |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|---------------|------------------------|
| Material fork | Stainless steel, heavy |
| Fork shape | Broad |
| Colour | Stainless steel |

FITTING

| | |
|-----------------------------|-------------------------|
| Fitting type | Small rectangular plate |
| Plate length | 100 mm |
| Plate width | 85 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 60 mm |
| Plate hole width (Minimum) | 77 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 9 mm |

ALPHA STAINLESS

8478PID125P62

EAN 4031582381702
Order number 00035730



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

