

PRODUCT INFORMATION

NOVATECH

FTP 400X80-Ø40 HL90

EAN 4031582319507
Order number 00802486



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	400 mm
Tread width	80 mm
Axle hole diameter	40 mm
Hub length	90 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	3000 kg
Load capacity at 6 km/h	2500 kg
Load capacity Static	5000 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	23.598 kg

NOVATECH

FTP 400X80-Ø40 HL90

EAN 4031582319507
Order number 00802486



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

