

# COVER DESIGN

2076XSP125R36-32S30

EAN 4031582358049



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |   |
|-----------------------------|---|
| Product name                | Cover design                            |
| Type                        | Swivel castor with central , total lock |
| Standard                    | EN12530 - Devices Castors               |
| Load capacity at 1.8 mph    | 220.46 lb                               |
| Electric conductive         | ✓                                       |
| Load capacity Static        | 440.92 lb                               |
| Temperature range (Minimum) | -4 °F                                   |
| Temperature range (Maximum) | 140 °F                                  |
| Overall height              | 6.42 in                                 |

## WHEEL


|                       |   |
|-----------------------|---|
| Body material         | Polyamide, electric conductive              |
| Tread material        | Polyurethane, injected, electric-conductive |
| Bearing               | Precision ball bearing                      |
| Threadguards          | With threadguard                            |
| Diameter              | 4.92 in                                     |
| Tread width           | 1.26 in                                     |
| Hardness of tread (A) | 87 Shore A                                  |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material            | Steel sheet, medium |
| Fork shape          | Closed              |
| Swivel bearing      | Two ball races      |
| Offset              | 1.61 in             |
| Swivel radius       | 4.07 in             |
| Swivel interference | 8.15 in             |

## FITTING

|               |  |
|---------------|--|
| Fitting type  | Stem with cam hole for profile bars, short version |
| Bolt diameter | 1.26 in  |
| Bolt length   | 1.97 in  |



Red Dot  
Design  
Award

# COVER DESIGN

2076XSP125R36-32S30


EAN 4031582358049



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---



Red Dot  
Design  
Award