

SUPRATECH

PJR100X32-Ø12 HL44,4 BLUE

EAN 4031582355185



BETTER MOBILITY. BETTER LIFE.

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
------------------------	-----------

Buka u pokretu	● ● ● ○ ○
----------------	-----------

Ishrana	● ● ● ○ ○
---------	-----------

otpornost na rdju	● ● ● ○ ○
-------------------	-----------

OSNOVNI ATRIBUTI

Naziv proizvoda	Supratech
Tip	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,136 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	kotrljajući lezaj
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	32 mm
dimenzija rupa osovina	12 mm
dužina glavnice	44,4 mm

SUPRATECH

PJR100X32-Ø12 HL44,4 BLUE

EAN 4031582355185



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

