

LINEA LIGHT

5925UAP100L51-11 RAL9011

EAN 4031582434910



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll performance	● ● ● ○ ○
------------------	-----------

Movement noise	● ● ● ○ ○
----------------	-----------

Attrition	● ● ● ○ ○
-----------	-----------

Corrosion resistance	● ● ● ● ○
----------------------	-----------

CORE ATTRIBUTES

Product name	Linea light
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	100 mm
Overall width	73 mm
Overall weight	0.418 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	20 mm

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	32 mm
Swivel radius	102 mm
Swivel interference	204 mm
Dome diameter	40 mm

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	11 mm

Deutscher
Designer
ClubInterzum
AwardIF
Design
Award

LINEA LIGHT

5925UAP100L51-11 RAL9011

EAN 4031582434910



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

