

# AGILA CARE

2476XSP100R36-32S30 4XM6

EAN 4031582358186



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                        |
|-----------------------------|----------------------------------------|
| Product name                | Agila care                             |
| Housing type                | Swivel castor with central, total lock |
| Standard                    | EN12530 - Devices Castors              |
| Load capacity at 3 km/h     | 100 kg                                 |
| Electric conductive         | ✓                                      |
| Load capacity Static        | 200 kg                                 |
| Temperature range (Minimum) | -20 °C                                 |
| Temperature range (Maximum) | 60 °C                                  |
| Overall height              | 138 mm                                 |
| Overall weight              | 0.869 kg                               |

## WHEEL

|                       |                                             |
|-----------------------|---------------------------------------------|
| Body material         | Polyamide, electric conductive              |
| Tread material        | Polyurethane, injected, electric-conductive |
| Bearing               | Precision ball bearing                      |
| Threadguards          | With threadguard                            |
| Diameter              | 100 mm                                      |
| Tread width           | 32 mm                                       |
| Hardness of tread (A) | 87 Shore A                                  |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Offset              | 38 mm               |
| Swivel radius       | 88 mm               |
| Swivel interference | 176 mm              |

## FITTING

|               |                                                    |
|---------------|----------------------------------------------------|
| Fitting type  | Stem with cam hole for profile bars, short version |
| Bolt diameter | 32 mm                                              |
| Bolt length   | 50 mm                                              |

# AGILA CARE

2476XSP100R36-32S30 4XM6

EAN 4031582358186



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

