

FORMA

6941UFP150R05-28 WHITE

EAN 4031582476507



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------------|
| Product name | Forma |
| Housing type | Swivel castor with directional lock |
| Load capacity at 3 km/h | 135 kg |
| Temperature range (Minimum) | -18 °C |
| Temperature range (Maximum) | 120 °C |
| Overall height | 205 mm |

WHEEL

| | |
|-----------------------|---------------------------------------|
| Body material | Polyamide |
| Tread material | Elastic tire, non-marking, vulcanized |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 150 mm |
| Tread width | 18 mm |
| Hardness of tread (A) | 60 Shore A |

HOUSING

| | |
|----------------|------------------------------|
| Material fork | Zinc-die-casting / Aluminium |
| Fork shape | Twin wheel housing |
| Swivel bearing | Precision ball bearing |
| Offset | 57 mm |
| Swivel radius | 137 mm |

FITTING

| | |
|---------------|-------------------|
| Fitting type | Solid stem, round |
| Bolt diameter | 28 mm |
| Bolt length | 40 mm |

FORMA

6941UFP150R05-28 WHITE

EAN 4031582476507



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

