

# ANIKA

5923UAI065L51-10 DOM18

EAN 4031582437782



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Anika
Type	Swivel castor with intermittend brake
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	67 mm
Overall width	39.5 mm
Overall weight	0.075 kg

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	65 mm
Tread width	11 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	20 mm
Swivel radius	55.4 mm
Swivel interference	110 mm
Dome diameter	18 mm

## FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm



PRODUCT INFORMATION

# ANIKA

5923UAI065L51-10 DOM18


EAN 4031582437782



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---



Interzum  
Award