

GLIDE

A229Y0I050B10-11X20/10 9011/1016

EAN 4031582319613
Order number 00075112



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Glide
Housing type	Customized solution
Electric conductive	✓
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	1.3 in
Overall width	1.97 in
Overall weight	0.14 lb

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	1.97 in
Hardness of tread (D)	65 Shore D

HOUSING

Material	Polypropylene
Fork shape	Straight
Swivel bearing	Stem, swiveling
Color	Graphite black (RAL9011)
Dome diameter	1.5 in
Collar diameter	1.97 in

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in
Stem length	0.79 in

PRODUCT INFORMATION

GLIDE

A229Y0I050B10-11X20/10 9011/1016

EAN 4031582319613
Order number 00075112



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

