

DIZAJN POKLOPCA

2076PIP125R26-28S45

EAN 4031582360929



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Dizajn poklopca
Tip	Okreni Tocak sa centralnim , potpuna kocnica
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	163 mm

TOCAK

Materijal za telo	polipropilen
	mekan
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	32 mm
Teškoća gazaćeg omotac (A)	75 Šor A

KUCISTE

Materijal	Čelični list, srednji
oblik viljuska	Zatvoreno
okretni lezaj	Dve lopte
ofset	41 mm
okretni radijus	103,5 mm
Otpor okretanju	207 mm

PRILAGODAVANJE

Tip uklapanja	stablo sa bregasta rupa za trake profila
Prečnik sraf	28 mm
Dužina sraf	96 mm

Red Dot Dizajn
Award

DIZAJN POKLOPCA

2076PIP125R26-28S45

EAN 4031582360929



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI



Red Dot Dizajn
Award