

DURATECH

TOP 085x65-Ø20 HL65

EAN 4031582331172



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	650 kg
Load capacity at 6 km/h	520 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1300 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.54 kg

WHEEL

Body material	Polyamide, heavy
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	85 mm
Tread width	65 mm
Axle Hole Diameter	20 mm
Hub Length	65 mm
Body width	65 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204

DURATECH

TOP 085x65-Ø20 HL65

EAN 4031582331172

Order number 00832611
Product Drawings



BETTER MOBILITY. BETTER LIFE.

