

# ALPHA

3470PVR100P30-13

EAN 4031582304190



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●○○○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha
Tip	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	75 kg
Statički Nosivost	150 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	128 mm
Ukupna težina	0,869 kg

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	35 mm
Teškoća gazećeg omotac (A)	85 Šora A

## KUCISTE

Materijal	Čelični list, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	40 mm
okretni radijus	90 mm
Otpor okretanju	180 mm

## PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	13 mm

# ALPHA

3470PVR100P30-13

EAN 4031582304190



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

3470...100P30-13

