

# ELASTECH

UFR125X40-Ø12 HL44,4 AZUL

EAN 4031582452907



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Body material         | Polyamide                             |
|                       | soft                                  |
| Tread material        | Elastic tire, non-marking, vulcanized |
| Bearing               | Roller bearing                        |
| Threadguards          | Without threadguard                   |
| Diameter              | 4.92 in                               |
| Tread width           | 1.57 in                               |
| Axle hole diameter    | 0.47 in                               |
| Hub length            | 1.75 in                               |
| Hardness of tread (A) | 64 Shore A                            |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Elastech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 551.16 lb                     |
| Load capacity Static        | 1102.31 lb                    |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 176 °F                        |
| Overall weight              | 0.93 lb                       |

# ELASTECH

UFR125X40-Ø12 HL44,4 AZUL

EAN 4031582452907



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

