

ALPHA

3470PVO125P30-13

EAN 4031582304121



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Alpha
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	155 mm
Overall weight	1.09 kg

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	40 mm
Swivel radius	102.5 mm
Swivel interference	205 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Solid rubber, black
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	125 mm
Tread width	37 mm
Hardness of tread (A)	85 Shore A

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

ALPHA

3470PVO125P30-13

EAN 4031582304121



BETTER MOBILITY. BETTER LIFE.

Product Drawings

