PRODUCT INFORMATION

LINEA

5925UAP075S70 10x15 RAL9002 TFR

EAN 4031582394528



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Linea
Type	Swivel caster with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	176.37 lb
Electric conductive	no
Stainless	no
Load capacity Static	352.74 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	3.23 in
Overall width	2.13 in

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Housing Color	Gray white (RAL9002)
Offset	0.91 in
Swivel radius	3.19 in
Swivel interference	6.38 in
Dome diameter	1.18 in
Thread diameter	0.39 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Axle	Riveted
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.59 in

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	0.39 in
Stem length	0.59 in

Deutscher Designer Club

Interzum Award

IF Design Award

© Copyright 2026 TENTE International GmbH


LINEA

5925UAP075S70 10x15 RAL9002 TFR

EAN 4031582394528

BETTER MOBILITY. BETTER LIFE.

Product Drawings



Deutscher Designer Club

Interzum Award

IF Design Award

© Copyright 2026 TENTE International GmbH