

PURETECH

DVR080x20-Ø8x45,5 + ASBUS

EAN 4031582331653



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	110.23 lb
Electric conductive	no
Stainless	no
Load capacity Static	220.46 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.6 lb

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	0.79 in
Axle hole diameter	0.31 in
Hub length	1.79 in
Hardness of tread (A)	85 Shore A

PURETECH

DVR080x20-Ø8x45,5 + ASBUS

EAN 4031582331653



BETTER MOBILITY. BETTER LIFE.

Product Drawings

