

ZETA

4687ITP160P63 SUPER CONVEX R25

EAN 4031582444605



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	500 kg
Load capacity Static	1000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	200 mm
Overall weight	3.484 kg

WHEEL

Body material	Aluminium
Tread profile	convex
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	55 mm
Swivel radius	161 mm
Swivel interference	322 mm

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ZETA

4687ITP160P63 SUPER CONVEX R25

EAN 4031582444605



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

