

# DURATECH HEAT

WOG 075X25 HL31,8 BLACK

EAN 4031582382891  
Order number 00039564



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Black
Diameter	75 mm
Tread width	25 mm
Axle hole diameter	8 mm
Hub length	31.8 mm
Body width	25 mm
Hardness of tread (D)	80 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	50 kg
Stainless	✓
Load capacity Static	100 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	134 °C
Overall weight	0.084 kg

# DURATECH HEAT

WOG 075X25 HL31,8 BLACK

EAN 4031582382891  
Order number 00039564



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

