

ALPHA

3477PVR100P30-13

EAN 4031582305685



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Alpha
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	75 kg
Electric Conductive	No
Stainless	No
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	128 mm
Overall weight	1.01 kg

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	41 mm
Swivel radius	121 mm
Swivel interference	242 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Solid rubber, black
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Hardness of tread (A)	85 Shore A

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

ALPHA

3477PVR100P30-13

EAN 4031582305685



BETTER MOBILITY. BETTER LIFE.

Product Drawings

