

# PURETECH AIR

DQP400X100-Ø10 HL74 4PLY WITH AXLE

EAN 4031582438215



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                               |
|-----------------------|-------------------------------|
| Body material         | Sheet Steel                   |
| Tread hardness        | soft                          |
| Tread material        | Pneumatic tyre, block profile |
| Bearing               | Precision ball bearing        |
| Threadguards          | With threadguard              |
| Diameter              | 400 mm                        |
| Tread width           | 100 mm                        |
| Axle hole diameter    | 10 mm                         |
| Hub length            | 74 mm                         |
| Hardness of tread (A) | 55 Shore A                    |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                         |              |
|-------------------------|--------------|
| Product name            | Puretech air |
| Type                    | Wheel        |
| Load capacity at 3 km/h | 200 kg       |
| Load capacity Static    | 400 kg       |
| Overall weight          | 2.665 kg     |

# PURETECH AIR

DQP400X100-Ø10 HL74 4PLY WITH AXLE

EAN 4031582438215



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

