

STEM

S70-8X25 / 10

EAN 4031582424669



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 1.8 mph	110.23 lb
Load capacity Static	220.46 lb
Overall height	0.24 in
Overall weight	0.07 lb

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	0.31 in
Stem length	0.98 in