PRODUCT INFORMATION

DURATECH

TOP 250x50-Ø20 HL60

EAN 4031582366266



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D
Bearing type	6205

PERFORMANCE

Roll Performance	●●●●●
Movement Noise	●●○○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1320 kg
Load capacity at 6 km/h	1100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	2200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	1.88 kg

© Copyright 2026 TENTE International GmbH


DURATECH

TOP 250x50-Ø20 HL60

EAN 4031582366266

Order number 00832580

Product Drawings




© Copyright 2026 TENTE International GmbH

DURATECH

TOP 250x50-Ø20 HL60

EAN 4031582366266

Order number 00837180



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH