PRODUCT INFORMATION

DURATECH

TOP 065x32-Ø12 HL32

EAN 4031582332315



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	639.34 lb
Load capacity at 3.7 mph	529.11 lb
Electric conductive	no
Stainless	no
Load capacity Static	1058.22 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.37 lb

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	1.26 in
Axle hole diameter	0.47 in
Hub length	1.26 in
Body width	1.26 in
Hardness of tread (D)	75 Shore D
Bearing type	6201

© Copyright 2026 TENTE International GmbH


DURATECH

TOP 065x32-Ø12 HL32

EAN 4031582332315

Order number 00829018

Product Drawings




© Copyright 2026 TENTE International GmbH

DURATECH

TOP 065x32-Ø12 HL32

EAN 4031582332315

Order number 00820018



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH