

# NOVATECH

FTP 400X100-Ø40 HL120

EAN 4031582319491  
Broj porudžbine 00801334

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	400 mm
Širina omotac	100 mm
dimenzija rupa osovina	40 mm
dužina glavcine	120 mm
Širina tela	100 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja ● ● ● ● ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ○

otpornost na rdju ● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	3840 kg
Nosivost na 6 km/h	3200 kg
Statički Nosivost	6400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	28,235 kg

# NOVATECH

FTP 400X100-Ø40 HL120

EAN 4031582319491  
Broj porudžbine 00801334



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

