

PRODUCT INFORMATION

BASETECH

POO3x1.25-Ø0.5 HL 40

EAN 4031582436082



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	76.2 mm
Tread width	31.75 mm
Axle Hole Diameter	12.1 mm
Hub Length	40 mm
Hardness of tread (D)	66 Shore D

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Basetech
Type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	115 kg
Electric Conductive	No
Stainless	No
Load capacity Static	230 kg

BASETECH

POO3x1.25-Ø0.5 HL 40

EAN 4031582436082



BETTER MOBILITY. BETTER LIFE.

Product Drawings

