

PRODUCT INFORMATION

BASETECH

POR080X34-Ø12 RAL9011

EAN 4031582320763  
Order number 00030950



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Identical with wheel body |
| Bearing               | Roller bearing            |
| Threadguards          | Without threadguard       |
| Diameter              | 3.15 in                   |
| Tread width           | 1.34 in                   |
| Axle hole diameter    | 0.47 in                   |
| Hub length            | 1.75 in                   |
| Hardness of tread (D) | 65 Shore D                |

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Basetech                      |
| Housing type                | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 275.58 lb                     |
| Load capacity Static        | 551.16 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 0.22 lb                       |

# BASETECH

POR080X34-Ø12 RAL9011

EAN 4031582320763  
Order number 00030950



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

