PRODUCT INFORMATION

ELASTECH

IEP 125x50-Ø25 HL60

EAN 4031582319699



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel Color	Jet black (similar RAL9005)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Axle Hole Diameter	25 mm
Hub Length	60 mm
Body width	50 mm
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll Performance	●●○○○
Movement Noise	●●●●●
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	240 kg
Electric Conductive	No
Stainless	No
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	0.89 kg

© Copyright 2026 TENTE International GmbH


ELASTECH

IEP 125x50-Ø25 HL60

EAN 4031582319699

Order number 00829687

Product Drawings




© Copyright 2026 TENTE International GmbH

ELASTECH

IEP 125x50-Ø25 HL60

EAN 4031582319599

Order number 00329657



© Copyright 2026 TENTE International GmbH