PRODUCT INFORMATION

DURATECH

TOO 100x50-Ø20 HL60

EAN 4031582322491



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement Noise	●●○○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	720 kg
Load capacity at 6 km/h	600 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.38 kg

WHEEL

Body material	Polyamide, heavy
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	100 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D

© Copyright 2026 TENTE International GmbH


DURATECH

TOO 100x50-Ø20 HL60

EAN 4031582322491

Order number 00804809

Product Drawings




© Copyright 2026 TENTE International GmbH

DURATECH

TOO 100x50-Ø20 HL60

EAN 4031582322491

Order number 00804809



© Copyright 2026 TENTE International GmbH