PRODUCT INFORMATION

MAXTECH

DNP200x50-Ø20x50

EAN 4031582380996



Image may differ from the original product

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Load capacity at 3 km/h	75 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	150 kg
Overall weight	0.86 kg

WHEEL

Body material	Sheet Steel
Tread Material Mix	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	50 mm

© Copyright 2026 TENTE International GmbH


MAXTECH

DNP200x50-Ø20x50

EAN 4031582380996

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH