

MAXTECH

PAP5X1.25-Ø9.8 HL41

EAN 4031582436198



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	127 mm
Tread width	31.75 mm
Axle hole diameter	9.8 mm
Hub length	41 mm
Hardness of tread (D)	41 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	136 kg
Load capacity Static	272 kg

MAXTECH

PAP5X1.25-Ø9.8 HL41

EAN 4031582436198



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

